




TOMCAT NANO EDGE

USER GUIDE 使用说明

Ver 1.0 Pg 1/3

Overview 概观



WEIGHT
10 KG




OSCILLATION
4100 RPM

Usage 用法



ATTACH SCRUBBING PAD
放置机器



CLIP ON HANDLE
扣上夹子



CONNECT PLUG
链接两个插头



CONNECT PLUG
链接两个插头

Usage 用法



INSERT POWER PLUG
插入电源



PRESS TO SWITCH ON
按下按钮



PERFECT FOR CONNERS
适合角落